

Eaton 736V-BOX

Catalog Number: 736V-BOX

Eaton residential grade duplex receptacle, #14-12 AWG, 15A, Residential, Flush, 125V, Side wire, Ivory, Brass, Thermoplastic, 1-15R, Duplex, Screw, Thermoplastic, ED Box



Photo is representative

General specifications

Product Name	Catalog Number
Eaton residential grade duplex receptacle	736V-BOX
	UPC
	032664750670
Product Length/Depth	Product Height
1.31 in	4.19 in
Product Width	Product Weight
0.74 in	0.12 lb
Certifications	
cULus Listed	
Federal Specification Classification 6221	
02	

defaultTaxonomyAttributeLabel

Device type

Receptacle

Type

Duplex receptacle

Amperage Rating

15A

Voltage rating

125V

Contact material

Brass

Features

Non-grounding

Application

Residential

Device grade

Standard grade

Wiring method

Side wire

Number of wires

2

Mounting method

Flush

Number Of Poles

Two-pole

Style type

Standard

Material

Thermoplastic

Packaging type

ED Box

Color

Ivory

Connection type

Screw

Allowable wire size

Resources

Catalogs

[Residential Buyers Guide B-26](#)

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - 736V-BOX](#)

#14-12 AWG

NEMA configuration

1-15R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

Thermoplastic

Receptacle type

Duplex



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia