

Eaton 7543PMURF

Catalog Number: 7543PMURF

Eaton LV Unipak capacitor bank, UNIPAK, Low Voltage Fixed Capacitor Banks, 90A, 480V, Three-phase, 75 kVAR, Protected, Neon red blown-fuse indicating lights, Three slottedblade-type fuses, C1 Frame



Photo is representative

General specifications

Product Name	Catalog Number
Eaton LV Unipak capacitor bank	7543PMURF
UPC	Product Length/Depth
782116058860	10.6 in
Product Height	Product Width
26.3 in	12.1 in
Product Weight	Warranty
65 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	Catalog Notes
CSA Certified UL Listed	Multiply the 240V kVAR rating by 0.75 to calculate the kVAR value at 208V.

defaultTaxonomyAttributeLabel

Type

UNIPAK

Amperage Rating

90A

Fuse type

Three slottedblade type fuses with 200,000 ampere interrupting capacity

Phase

Three-phase

Product Category

Low Voltage Fixed Capacitor Banks

Voltage rating

480 V

Enclosure

NEMA 1, NEMA 3R

Enclosure material

14 gauge steel finished with durable powder coat finish

Frame size

C1

Indicators

Red, neon blown-fuse indicating lights are protected by transparent weatherproof guard

Protection

Three fuses, three lights

Rating

75 kVAR

Resources

Brochures

[Low voltage fixed and switched capacitor banks](#)

Catalogs

[Eaton's Volume 3—Power Distribution and Control Assemblies](#)

Specifications and datasheets

[Low Voltage Power Factor Correction Capacitor Banks and Harmonic Filters](#)

[Eaton Specification Sheet - 7543PMURF](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)