

# Eaton 7810GDA

Catalog Number: 7810GDA

Eaton manual motor controller, #14-10 AWG, 30A, Industrial, 600V, Front, Maintained, Orange, NEMA Type 1, Enclosure: Stainless steel, Three-pole, Three-phase, Single-throw, Glass-filled nylon

## General specifications



### Product Name

Eaton manual motor controller

### Catalog Number

7810GDA

### UPC

040893627618

### Product Length/Depth

3.75 in

### Product Height

2.38 in

### Product Width

2.38 in

### Product Weight

1.69 lb

### Certifications

cULus Listed



Powering Business Worldwide

## defaultTaxonomyAttributeLabel

### Enclosure

NEMA 1

### Type

Manual motor controller

### Amperage Rating

30A

### Voltage rating

600 V

### Number Of Poles

Three-pole

### Phase

Three-phase

### Enclosure material

Stainless steel

### Application

Industrial

### Device grade

Industrial

### Wiring method

Front

### Closure type

Maintained

### Allowable wire size

#14-10 AWG

### Material

Glass-filled nylon

### Throw

Single-throw

### Color

Orange

## Resources

### Brochures

[Wiring Devices Buyer's Guide](#)

### Specifications and datasheets

[Eaton Specification Sheet - 7810GDA](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)