

Eaton 7810UDST

Catalog Number: 7810UDST

Eaton manual motor controller, #14-10 AWG, 30A, Industrial, 600V, Front, Short toggle, Maintained, Gray, NEMA Type 1, Enclosure: Stainless steel, Three-pole, Three-phase, Short toggle, Single-throw, Glass-filled nylon

General specifications

Product Name	Catalog Number
Eaton manual motor controller	7810UDST
UPC	Product Length/Depth
040893681825	2.5 in
Product Height	Product Width
3.88 in	2.5 in
Product Weight	Certifications
0.38 lb	cULus Listed

defaultTaxonomyAttributeLabel

Enclosure

NEMA 1

Type

Manual motor controller

Amperage Rating

30A

Voltage rating

600 V

Number Of Poles

Three-pole

Phase

Three-phase

Enclosure material

Stainless steel

Application

Industrial

Device grade

Industrial

Wiring method

Front

Switch type

Short toggle

Closure type

Maintained

Allowable wire size

#14-10 AWG

Material

Glass-filled nylon

Throw

Single-throw

Actuator

Short toggle

Color

Gray

Resources

Brochures

[Wiring Devices Buyer's Guide](#)

Specifications and datasheets

[Eaton Specification Sheet - 7810UDST](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)