

Eaton 817BK

Catalog Number: 817BK

Eaton commercial specification grade single receptacle, #14-10 AWG, 15A, Commercial, Flush, 125V, Side wire, Black, Brass, Nylon, 5-15R, Single, Screw, PVC, Core pack



General specifications

Product Name	Catalog Number
Eaton commercial specification grade single receptacle	817BK
	UPC
	032664563546
Product Length/Depth	Product Height
1.31 in	3.28 in
Product Width	Product Weight
0.83 in	0.18 lb

Certifications

cULus Listed
NOM
Federal Specification Classification 6233
01

defaultTaxonomyAttributeLabel

Device type

Receptacle

Type

Single receptacle

Amperage Rating

15A

Voltage rating

125V

Contact material

Brass

Features

Auto-grounding

Application

Commercial

Device grade

Commercial

Wiring method

Side wire

Number of wires

3

Mounting method

Flush

Number Of Poles

Two-pole

Style type

Standard

Material

PVC

Packaging type

Core pack

Color

Black

Connection type

Screw

Allowable wire size

Resources

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - 817BK](#)

[Commercial grade straight blade duplex receptacles spec sheet](#)

#14-10 AWG

NEMA configuration

5-15R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

Nylon

Receptacle type

Single



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)