

Eaton 827B-BOX

Catalog Number: 827B-BOX

Eaton commercial specification grade duplex receptacle, #14-10 AWG, 15A, Commercial, Flush, 125V, Side wire, Brown, Brass, Nylon, 5-15R, Duplex, Screw, Nylon, ED Box



Photo is representative

General specifications

Product Name	Catalog Number
Eaton commercial specification grade duplex receptacle	827B-BOX
	UPC
	032664182808
Product Length/Depth	Product Height
4.25 in	1.13 in
Product Width	Product Weight
1.75 in	0.001 lb
Compliances	Certifications
RoHS Compliant	cULus Listed
	NOM
	Federal Specification Classification 6233 01

defaultTaxonomyAttributeLabel

Device type

Receptacle

Type

Duplex receptacle

Amperage Rating

15A

Voltage rating

125V

Contact material

Brass

Application

Commercial

Device grade

Commercial

Wiring method

Side wire

Number of wires

3

Mounting method

Flush

Number Of Poles

Two-pole

Style type

Standard

Material

Nylon

Packaging type

ED Box

Color

Brown

Connection type

Screw

Allowable wire size

#14-10 AWG

NEMA configuration

Resources

Brochures

[Wiring Devices Buyer's Guide](#)

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - 827B-BOX](#)

5-15R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

Nylon

Receptacle type

Duplex



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)