

Eaton 829W-BOX

Catalog Number: 829W-BOX

Eaton commercial specification grade duplex receptacle, #14-10 AWG, 15A, Commercial, Flush, 125/250V, Side wire, White, Brass, Nylon, 5-15R, 6-15R, Duplex, Screw, Nylon, ED Box



Photo is representative

General specifications

Product Name	Catalog Number
Eaton commercial specification grade duplex receptacle	829W-BOX
	UPC
	032664748943
Product Length/Depth	Product Height
1.3 in	4.19 in
Product Width	Product Weight
0.82 in	0.001 lb

Certifications

UL
Federal Specification Classification 6233
01

defaultTaxonomyAttributeLabel

Device type

Receptacle

Type

Dual voltage

Amperage Rating

15A

Voltage rating

125/250 V

Contact material

Brass

Features

Auto-grounding

Dual voltage

Application

Commercial

Device grade

Commercial

Wiring method

Side wire

Number of wires

3

Mounting method

Flush

Number Of Poles

Two-pole

Style type

Standard

Material

Nylon

Packaging type

ED Box

Color

White

Connection type

Screw

Resources

Multimedia

Residential straight blade receptacles

Specifications and datasheets

Eaton Specification Sheet - 829W-BOX

Commercial grade straight blade duplex receptacles spec sheet

Allowable wire size

#14-10 AWG

NEMA configuration

5-15R, 6-15R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

Nylon

Receptacle type

Duplex



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)