

Eaton 8300LA

Catalog Number: 8300LA

Eaton Arrow Hart heavy-duty hospital grade duplex receptacle, #14-10 AWG, 20A, Healthcare, Flush, 125V, Back and side, Light almond, Brass, High-impact nylon face, PVC base, 5-20R, Duplex, Screw, Nylon, PVC



General specifications

Product Name	Catalog Number
Eaton Arrow Hart heavy-duty hospital grade duplex receptacle	8300LA
	UPC
	032664719738
Product Length/Depth	Product Height
1.3 in	4.19 in
Product Width	Product Weight
0.88 in	0.001 lb

Certifications

UL
NOM
Federal Specification Classification 6233
01

defaultTaxonomyAttributeLabel

Device type

Receptacle

Type

Duplex receptacle

Amperage Rating

20A

Voltage rating

125V

Contact material

Brass

Features

Auto-grounding

Application

Healthcare

Device grade

Heavy-duty hospital grade

Wiring method

Back and side

Number of wires

3

Mounting method

Flush

Number Of Poles

Two-pole

Style type

Standard

Material

Nylon, PVC

Color

Light almond

Connection type

Screw

Allowable wire size

#14-10 AWG

Resources

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - 8300LA](#)

[Arrow Hart heavy-duty hospital grade straight blade duplex receptacles](#)

NEMA configuration

5-20R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

High-impact nylon face

PVC base

Receptacle type

Duplex



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)