

# Eaton 83-BOX

Catalog Number: 83-BOX

Eaton Arrow Hart extra heavy-duty angled plug , #12-10 AWG, 30A, Commercial, 125V, Back wire, Black, Brass, Urea, TT-30P, Two-pole, three-wire, grounding, Screw, 0.64", Thermoplastic, ED Box

Photo is representative

## General specifications

Product Name	Catalog Number
Eaton Arrow Hart extra heavy-duty angled plug	83-BOX
	UPC
	032664752216

Product Length/Depth	Product Height
3.88 in	2.25 in

Product Width	Product Weight
2.94 in	0.268 lb

## Certifications

UL  
NOM  
Federal Specification Classification 6221  
02



## defaultTaxonomyAttributeLabel

### Device type

Plug

### Special features

Travel trailer

### Type

Angled plug

### Amperage Rating

30A

### Voltage rating

125V

### Contact material

Brass

### Features

Travel trailer

### Application

Commercial

### Device grade

Extra heavy-duty industrial specification grade

### Wiring method

Back wire

### Number of wires

3

### Number Of Poles

Two-pole

### Style type

Power, Angled body

### Cord range

0.64"

### Material

Thermoplastic

### Packaging type

ED Box

### Color

Black

## Resources

### Brochures

[Flush mount receptacles sell sheet](#)

### Catalogs

[Residential Buyers Guide B-44](#)

### Specifications and datasheets

[Eaton Specification Sheet - 83-BOX](#)

Connection type

Screw

Allowable wire size

#12-10 AWG

NEMA configuration

TT-30P

Torque rating

20-24 lbf-inch

Design type

Straight blade

Face/body material

Urea

Receptacle type

Two-pole, three-wire, grounding



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)