

# Eaton 83-SP

Catalog Number: 83-SP

Eaton Arrow Hart extra heavy-duty angled plug , #12-10 AWG, 30A, Commercial, 125V, Back wire, Black, Brass, Urea, TT-30P, Two-pole, three-wire, grounding, Screw, 0.64", Thermoplastic, Retail Box



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Arrow Hart extra heavy-duty angled plug	83-SP
	<b>UPC</b>
	032664206108
<b>Product Length/Depth</b>	<b>Product Height</b>
2.38 in	4 in
<b>Product Width</b>	<b>Product Weight</b>
3 in	0.313 lb

## Certifications

UL  
NOM  
Federal Specification Classification 6221  
02

## defaultTaxonomyAttributeLabel

### Device type

Plug

### Special features

Travel trailer

### Type

Angled plug

### Amperage Rating

30A

### Voltage rating

125V

### Contact material

Brass

### Features

Travel trailer

### Application

Commercial

### Device grade

Extra heavy-duty industrial specification grade

### Wiring method

Back wire

### Number of wires

3

### Number Of Poles

Two-pole

### Style type

Power, Angled body

### Cord range

0.64"

### Material

Thermoplastic

### Packaging type

Retail Box

### Color

Black

## Resources

### Brochures

Flush mount receptacles sell sheet

### Catalogs

Residential Buyers Guide B-44

### Specifications and datasheets

Eaton Specification Sheet - 83-SP

Connection type

Screw

Allowable wire size

#12-10 AWG

NEMA configuration

TT-30P

Torque rating

20-24 lbf-inch

Design type

Straight blade

Face/body material

Urea

Receptacle type

Two-pole, three-wire, grounding



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)