

# Eaton 9505SG

Catalog Number: 9505SG

Eaton ASPIRE residential grade decorator duplex receptacle, #14-10 AWG, 15A, Commercial|Residential, Flush, 125V, Back and side, Silver granite, Brass, High-impact nylon face, Polycarbonate base, 5-15R, Duplex, Screw, Nylon, Thermoplastic, Core pack



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton ASPIRE residential grade decorator duplex receptacle	9505SG
	<b>UPC</b>
	032664645563
<b>Product Length/Depth</b>	<b>Product Height</b>
1.3 in	3.81 in
<b>Product Width</b>	<b>Product Weight</b>
0.69 in	0.15 lb
<b>Compliances</b>	<b>Certifications</b>
RoHS Compliant	UL
	NOM
	Federal Specification Classification 6233 01

## defaultTaxonomyAttributeLabel

### Device type

Receptacle

### Type

Duplex receptacle

### Amperage Rating

15A

### Voltage rating

125V

### Contact material

Brass

### Application

Commercial/residential

### Device grade

Standard grade

### Wiring method

Back and side

### Number of wires

3

### Mounting method

Flush

### Number Of Poles

Two-pole

### Style type

Decorator

### Material

Nylon, Thermoplastic

### Packaging type

Core pack

### Color

Silver granite

### Connection type

Screw

### Allowable wire size

#14-10 AWG

## Resources

### Brochures

[Aspire design collection brochure](#)

### Multimedia

[Residential straight blade receptacles](#)

### Specifications and datasheets

[Eaton Specification Sheet - 9505SG](#)

NEMA configuration

5-15R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

Polycarbonate base

High-impact nylon face

Receptacle type

Duplex



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)