

Eaton 9505WS

Catalog Number: 9505WS

Eaton ASPIRE residential grade decorator duplex receptacle, #14-10 AWG, 15A, Commercial|Residential, Flush, 125V, Back and side, White satin, Brass, High-impact nylon face, Polycarbonate base, 5-15R, Duplex, Screw, Thermoplastic, Core pack



General specifications

Product Name	Catalog Number
Eaton ASPIRE residential grade decorator duplex receptacle	9505WS
	UPC
	032664645570
Product Length/Depth	Product Height
1.3 in	3.81 in
Product Width	Product Weight
0.69 in	0.169 lb
Compliances	Certifications
RoHS Compliant	UL
	NOM
	Federal Specification Classification 6233 01

defaultTaxonomyAttributeLabel

Device type

Receptacle

Type

Duplex receptacle

Amperage Rating

15A

Voltage rating

125V

Contact material

Brass

Application

Commercial/residential

Device grade

Standard grade

Wiring method

Back and side

Number of wires

3

Mounting method

Flush

Number Of Poles

Two-pole

Style type

Decorator

Material

Thermoplastic

Packaging type

Core pack

Color

White satin

Connection type

Screw

Allowable wire size

#14-10 AWG

Resources

Brochures

[Aspire design collection brochure](#)

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - 9505WS](#)

NEMA configuration

5-15R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

Polycarbonate base

High-impact nylon face

Receptacle type

Duplex



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)