

Eaton 9507TRDS

Catalog Number: 9507TRDS

Eaton ASPIRE residential grade decorator single receptacle, #14-10 AWG, 15A, Commercial|Residential, Flush, 125V, Push and side, Desert sand, Brass, High-impact nylon face, Polycarbonate base, 5-15R, Single, Screw, Thermoplastic, Core pack



General specifications

Product Name	Catalog Number
Eaton ASPIRE residential grade decorator single receptacle	9507TRDS
	UPC
	032664665509
Product Length/Depth	Product Height
1.3 in	3.81 in
Product Width	Product Weight
0.69 in	0.02 lb
Compliances	Certifications
RoHS Compliant	cULus Listed NOM

defaultTaxonomyAttributeLabel

Device type

Receptacle

Type

Single receptacle

Amperage Rating

15A

Voltage rating

125V

Contact material

Brass

Features

Tamper resistant

Application

Commercial/residential

Device grade

Standard grade

Wiring method

Push and side

Number of wires

3

Mounting method

Flush

Number Of Poles

Two-pole

Style type

Standard

Material

Thermoplastic

Packaging type

Core pack

Color

Desert sand

Connection type

Screw

Resources

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - 9507TRDS](#)

[Aspire TR single and duplex receptacle spec sheet](#)

Allowable wire size

#14-10 AWG

NEMA configuration

5-15R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

Polycarbonate base

High-impact nylon face

Receptacle type

Single



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)