

Eaton 9PX5KP2

Catalog Number: 9PX5KP2

Eaton 9PX UPS, Network card included, 6U, 5000 VA, 4500 W, Hardwired input, Outputs: Hardwired, 120/240V

General specifications



Product Name	Catalog Number
Eaton 9PX UPS	9PX5KP2
UPC	Product Length/Depth
743172039798	28.4 in
Product Height	Product Width
10.2 in	17.3 in
Product Weight	Warranty
201 lb	3 year limited
Compliances	Certifications
FCC Part 15	cULus Listed
CE Marked	NOM
CISPR22 Class A / FCC part 15 Class A	IEC 62040-2:2006 Cat C2
	ENERGY STAR certified

Battery

Runtime graph

[View runtime graph](#)

Battery management

ABM technology (3-stage charging extends battery service life by 50% and provides advance warning for battery replacement)

Battery replacement

Hot-swappable internal batteries and extended battery modules (EBMs)

Battery type

Sealed, lead-acid

Extended battery capability

Add up to 4 extended battery modules (EBM). Part number 9PXEBM180RT

Electrical output

Receptacle

Hardwired

Topology

Online/Double-conversion

Wattage

4500 W

VA rating

5000 VA

Output waveform

True sine wave

Voltage

120/208V

Output power factor

0.9

Output nominal voltage

208V default (200/208/220/230/240V)

Output voltage range

±1% steady-state

Output frequency

50/60 Hz

Electrical input

Input connection

Hardwired

Input nominal voltage

208V default (200/208/220/230/240V)

Input frequency range

60 Hz: 50–70 Hz, 50 Hz: 40–60 Hz

Input power factor

>0.99 typical

Communications

Communication

Web/SNMP in MiniSlot expansion port + 1 USB port + 1 serial RS232 port + 1 mini-terminal block for remote ON/OFF + 1 mini-terminal block for remote power off + 1 mini-terminal block for output relay Communication slot

Expansion slots

(1) Mini-Slot (MS) expansion port with Gigabit Network Card (NETWORK-M2) included

Ethernet interface

Yes

Includes network card

Yes

Software compatibility

Intelligent Power Software Suite

User interface

Graphical display, 5-button programmable menu

Environmental

Altitude

<1000m for nominal power, 10% power degrading every 1000m (up to 3000m)

BTU Rating

Online: 1186, Battery: 1608

Noise level

<45 dB at 1 meter

Relative humidity

0-95% non-condensing

Temperature range

0° to 40°C (32° to 104°F)

Additional specifications

Special features

Gigabit Network Card (NETWORK-M2) included

Form factor

Rack/tower

Rack size

6U

Rack mounting kit

Yes

Efficiency

93%

Package contents

9PX5K 5 kVA UPS
9PXPPDM2 HW PowerPass
Distribution Module
Gigabit Network Card
(Network-M2)
4-post rail kit
User manual
Quick start guide
Tower pedestals
Intelligent Power Software
Suite CD
RS-232 serial cable
USB cable

Warranty and support

Standard factory warranty

3-YEAR FACTORY
WARRANTY
- 3 years
- Parts, electronics and
batteries coverage
- Standard ground shipping
- Technical support

Extended service plans

ADVANCED DEPOT
EXCHANGE
- 5-year depot repair:
9SW5Y-6000UC
- Expedited parts coverage
for 5 years
- Parts, electronics and UPS
batteries coverage
- Next business day
shipping
- Technical support
5-YEAR ON-SITE PLAN:
WFLN75XX-6009UC
- On-site parts and labor
coverage for years 5
- Parts, electronics and UPS
batteries coverage

Cable gland for hardwire connection
Phillips head screw driver

Internal bypass

Yes

- 24x7 on-site labor coverage, next-day response
- Next-day shipping
- Technical support

Resources

Brochures

[Eaton 9PX 5-11 kVA UPS brochure](#)

[9PX UPS bundles configuration overview](#)

Drawings

[9PXPPDM2 Pro-E drawing](#)

[Battery Integration System Pro-E drawing](#)

[9PX5K Pro-E drawing](#)

Manuals and user guides

[9PX battery integration system user guide](#)

[9PX PPDM and transformers user guide](#)

[9PX UPS \(5-6 kVA\) user guide](#)

Specifications and datasheets

[9PX technical specifications: 5 and 6 kVA](#)

[Eaton Specification Sheet - 9PX5KP2](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)