

# Eaton A200M0CWDJ1

Catalog Number: A200M0CWDJ1

Non-Reversing Starter, 240V/60 Hz coil voltage, 18A, Three-pole, Size 0, 1 hp at 115V, 3 hp at 208,240V, 5 hp at 480,600V, A200 series, Type A Auto Reset



Photo is representative

## General specifications

### Product Name

Eaton A200 NEMA motor control

### Catalog Number

A200M0CWDJ1

### UPC

782116053490

### Product Length/Depth

1 in

### Product Height

1 in

### Product Width

1 in

### Product Weight

0.1 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

CSA Certified

### Catalog Notes

For ambient compensated overload relay with auto-reset, add Suffix D.

Accessories

Motor control

Phase

Three-phase magnetic

Size

0

Amperage rating

18A

Series

A200

Special features

Without lugs

Horsepower

1 hp at 115V, 3 hp at 208/240V, 5 hp at 480/600 V

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Installation instructions

[Instructions for A200, A210, A250 size 6, two- or three-pole non-reversing or reversing motor controllers](#)

Specifications and datasheets

[Eaton Specification Sheet - A200M0CWDJ1](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)