

Eaton A27CGD25B032

Catalog Number: A27CGD25B032

Eaton definite purpose starter, 25 A, Coil: 208-240 V, 50/60 Hz, 24-32 FLA, Common control wiring, NEMA Type 1 Enclosed, 25 A IFL, 24-32 FLA, Three-phase, Screw/pressure plate and quick connect terminals (side-by-side), Non-reversing



Photo is representative

General specifications

Product Name	Catalog Number
Eaton definite purpose starter	A27CGD25B032
UPC	Product Length/Depth
786685458311	5.81 in
Product Height	Product Width
10.17 in	5.63 in
Product Weight	Warranty
4.8 lb	1 year
Certifications	
UL Recognized	
CSA Certified	

Amperage Rating

25A

Phase

Three-phase

Type

Non-reversing

Overload relay

24-32 FLA

Coil

208-240 Vac, 50/60 Hz

Control characteristics

Common control

Enclosure

NEMA type 1 enclosed

Inductive full load

25 A IFL

Overload range

24-32 A

Terminals

Screw/pressure plate and quick connect terminals (side-by-side)

Model

Starter

Specifications and datasheets

[Eaton Specification Sheet - A27CGD25B032](#)