

Eaton A27CGF30C024

Catalog Number: A27CGF30C024

Eaton definite purpose starter, 30 A, Coil: 440-480 V, 50/60 Hz, 16-24 FLA, Common control wiring, NEMA Type 1 Enclosed, 30 A IFL, 16-24 FLA, Three-phase, Box lugs and quick connect terminals (side-by-side), Non-reversing



Photo is representative

General specifications

Product Name	Catalog Number
Eaton definite purpose starter	A27CGF30C024
UPC	Product Length/Depth
786685458397	5.81 in
Product Height	Product Width
10.17 in	5.63 in
Product Weight	Warranty
4.8 lb	1 year

Certifications

CSA Certified
UL Recognized

Amperage Rating

30A

Phase

Three-phase

Type

Non-reversing

Overload relay

16-24 FLA

Coil

440-480 Vac, 50/60 Hz

Control characteristics

Common control

Enclosure

NEMA type 1 enclosed

Inductive full load

30 A IFL

Overload range

16-24 A

Terminals

Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)

Model

Starter

Specifications and datasheets

Eaton Specification Sheet - A27CGF30C024