

# Eaton AA23AB

Catalog Number: AA23AB

NEMA A200 Thermal Overload Relay, Three-pole, Starter mounted, NEMA , Thermal Type A, Class 20, 1NC Auxiliary Contact, Alarm Contact (Form C), Ambient Compensated , Full load range 26.3-45A

## General specifications



Photo is representative

### Product Name

Eaton Freedom NEMA overload relay

### Catalog Number

AA23AB

### UPC

786678398488

### Product Length/Depth

6.1 in

### Product Height

5.2 in

### Product Width

5.6 in

### Product Weight

1.25 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed  
CSA Certified

### Catalog Notes

3-Pole Type B Overload Relay is a suitable alternative to a 3-Pole Type A Overload Relay in Manual Reset Mode

## defaultTaxonomyAttributeLabel

### Modification

1NC Auxiliary Contact, Alarm Contact (Form C), Ambient Compensated

### Design

NEMA

### Full load current range

26.3-45A

### Mounting

Starter

### Number Of Poles

Three-pole

### Special features

Heaters required

### Trip Type

Thermal Type A, Class 20

### Type

A200

## Resources

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

### Specifications and datasheets

[Eaton Specification Sheet - AA23AB](#)

### Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)