

Eaton AA33AB

Catalog Number: AA33AB

NEMA A200 Thermal Overload Relay, Three-pole, Starter mounted, NEMA , Thermal Type A, Class 20, 1NC Auxiliary Contact, Alarm Contact (Form C), Ambient Compensated , Full load range 19-90A

General specifications



Photo is representative

Product Name

Eaton Freedom NEMA overload relay

Catalog Number

AA33AB

UPC

786678226217

Product Length/Depth

8.2 in

Product Height

5.1 in

Product Width

6 in

Product Weight

2.1 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed
CSA Certified

Catalog Notes

3-Pole Type B Overload Relay is a suitable alternative to a 3-Pole Type A Overload Relay in Manual Reset Mode

defaultTaxonomyAttributeLabel

Modification

1NC Auxiliary Contact, Alarm Contact (Form C), Ambient Compensated

Design

NEMA

Full load current range

19-90A

Mounting

Starter

Number Of Poles

Three-pole

Special features

Heaters required

Trip Type

Thermal Type A, Class 20

Type

A200

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Specifications and datasheets

[Eaton Specification Sheet - AA33AB](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia