

# Eaton AA43AB

Catalog Number: AA43AB

NEMA A200 Thermal Overload Relay, Three-pole, Starter mounted, NEMA , Thermal Type A, Class 20, 1NC Auxiliary Contact, Alarm Contact (Form C), Ambient Compensated , Full load range 19-135A

## General specifications



Photo is representative

### Product Name

Eaton Freedom NEMA overload relay

### UPC

786678822709

### Product Height

5.2 in

### Product Weight

2.2 lb

### Certifications

UL Listed

CSA Certified

### Catalog Number

AA43AB

### Product Length/Depth

8.2 in

### Product Width

6 in

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Catalog Notes

3-Pole Type B Overload Relay is a suitable alternative to a 3-Pole Type A Overload Relay in Manual Reset Mode

## defaultTaxonomyAttributeLabel

### Modification

1NC Auxiliary Contact, Alarm Contact (Form C), Ambient Compensated

### Design

NEMA

### Full load current range

19-135A

### Mounting

Starter

### Number Of Poles

Three-pole

### Special features

Heaters required

### Trip Type

Thermal Type A, Class 20

### Type

A200

## Resources

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

### Specifications and datasheets

[Eaton Specification Sheet - AA43AB](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)