

Eaton AFU0333 50

Catalog Number: AFU0333 50

Eaton Crouse-Hinds series AFU conveyor belt control switch, 15A, Two normally open/two normally closed, Feraloy iron, 25 lb total oper force, Single end left, 15 lb without switch, (3) 1" hubs

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series AFU conveyor belt control switch	AFU0333 50
	UPC
	782274047126
Product Length/Depth	Product Height
12.92 in	5.68 in
Product Width	Product Weight
9.5 in	21.6 lb

Photo is representative

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class II, Division 1

Class II, Division 2

Class III

NEMA Rating

3

4

9

Ingress protection (IP) ratings

IP66

Product specifications

Type

Single end left

Weight without switch

15 lb

Total operating force required

25 lb

Contact arrangement

Two normally open, two normally closed

Amperage Rating

15A

Voltage rating

600 Vac

Number of hubs

3

Material

Feraloy iron alloy

Trade size

1"

Resources

Catalogs

[AFU and AFUX Series Explosionproof Conveyor Belt Control Switches catalog page](#)

Certification reports

[AFU and AFUX Explosionproof Conveyor Belt Control Switches UL certification](#)

[AFU and AFUX Explosionproof Conveyor Belt Control Switches Canadian certification](#)

Installation instructions

[IF 548 - AFU-K5 Safety Switch Kit](#)

[IF 958 - AFU/AFUX Model M7 Conveyor Control Safety Switches with Slack Condition](#)

[IF 493 - AFU Safety Switch](#)

Specifications and datasheets

[Eaton Specification Sheet - AFU0333 50](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)