

Eaton AH1201LTW

Catalog Number: AH1201LTW

Eaton Arrow Hart industrial grade toggle switch, Lighted, #14-10 AWG, 15A, Industrial, Flush, 120/277V, Back and side, Screw, White, Single-Pole, Single-Pole, Brass, Phenolic



General specifications

Product Name	Catalog Number
Eaton Arrow Hart industrial grade toggle switch	AH1201LTW
	UPC 032664706363
Product Length/Depth	Product Height
1.3 in	4.19 in
Product Width	Product Weight
1.075 in	0.37 lb
Certifications	
cULus Listed	
NOM	

defaultTaxonomyAttributeLabel

Special features

Lighted

Type

Toggle switch

Amperage Rating

15A

Voltage rating

120/277 V

Number Of Poles

Single-pole

Application

Industrial

Wiring method

Back and side

Switch type

Single-pole

Mounting method

Flush

Connector type

Screw

Material

Phenolic

Allowable wire size

#14-10 AWG

Torque rating

14 lbf-inch

Terminal enclosure material

Brass

Color

White

Resources

Multimedia

[Arrow Hart - Connecting Safety to Reliability since 1890](#)

Specifications and datasheets

[Eaton Specification Sheet - AH1201LTW](#)

[Arrow Hart extra heavy-duty industrial grade AC toggle switches spec sheet](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)