

Eaton AH1221W

Catalog Number: AH1221W

Eaton Arrow Hart industrial grade toggle switch, #14-10 AWG, 20A, Industrial, Flush, 120/277V, Back and side, Screw, White, Single-Pole, Single-Pole, Brass, Polycarbonate



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Arrow Hart industrial grade toggle switch	AH1221W
	UPC
	032664734694
Product Length/Depth	Product Height
1.3 in	4.19 in
Product Width	Product Weight
1.005 in	0.001 lb

Certifications

cULus Listed
NOM
Federal Specification Classification W-S-896E

defaultTaxonomyAttributeLabel

Type

Toggle switch

Amperage Rating

20A

Voltage rating

120/277 V

Number Of Poles

Single-pole

Application

Industrial

Wiring method

Back and side

Switch type

Single-pole

Mounting method

Flush

Connector type

Screw

Material

Polycarbonate

Allowable wire size

#14-10 AWG

Torque rating

14 lbf-inch

Terminal enclosure material

Brass

Terminals

0.031 in

Color

White

Resources

Multimedia

[Arrow Hart - Connecting Safety to Reliability since 1890](#)

Specifications and datasheets

[Eaton Specification Sheet - AH1221W](#)

[Arrow Hart extra heavy-duty industrial grade AC toggle switches spec sheet](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)