

Eaton AH5100R9W-15

Catalog Number: AH5100R9W-15

Eaton Arrow Hart pin and sleeve angled receptacle, Angled 15°; IP69K Rated, #4 -1/0 AWG, #12 - #16 AWG (pilot), 100A, 3ØY 120/208V, Back wire, Blue, Nickel plated brass, IP67, Nylon, Four-pole, Five-wire, AHBB100 Back box style, Female

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Arrow Hart pin and sleeve angled receptacle	AH5100R9W-15
	UPC
	032664740282

Product Length/Depth	Product Height
7.375 in	7.375 in

Product Width	Product Weight
6.25 in	3.32 lb

Certifications

Contact Manufacturer
cRUus

defaultTaxonomyAttributeLabel

Type

Receptacle

Amperage Rating

100A

Voltage rating

120/208 V

Contact material

Nickel plated brass

Application

Industrial, food and beverage, wastewater treatment

Number of wires

Grounding

5

Number Of Poles

Four-pole

Back box style

AHBB100

Environmental resistance

IP69K

IP67

Color

Blue

Gender

Female

Allowable wire size

#4 -1/0 AWG, #12-16 AWG (pilot)

Torque rating

70 lbf-inch

Design type

Pin and sleeve receptacle

Face/body material

Nylon

Material

Thermoplastic

Resources

Brochures

[Eaton IEC 60309 Arrow Hart pin and sleeve devices brochure](#)

Multimedia

[Pin and Sleeve Video](#)

Specifications and datasheets

[Eaton Specification Sheet - AH5100R9W-15](#)

[60A and 100A IEC 309 Watertight pin and sleeve devices spec sheet](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)