

Eaton AH5666BK

Catalog Number: AH5666BK

Eaton Arrow Hart quick grip straight blade plug, #16-12 AWG, 15A, Industrial, 250V, Back wire, Black, Brass, Nylon, 6-15P, Two-pole, three-wire, grounding, Screw, 0.22-0.66", Nylon, Core pack

General specifications



Product Name

Eaton Arrow Hart quick grip straight blade plug

Catalog Number

AH5666BK

UPC

032664734267

Product Length/Depth

1.67 in

Product Height

1.46 in

Product Width

1.96 in

Product Weight

0.129 lb

Compliances

RoHS Compliant

Certifications

UL

NOM

Federal Specification Classification 6221
02



Powering Business Worldwide

defaultTaxonomyAttributeLabel

Device type

Plug

Type

Plug

Amperage Rating

15A

Voltage rating

250V

Contact material

Brass

Application

Industrial

Device grade

Heavy-duty industrial specification grade

Wiring method

Back wire

Number of wires

3

Number Of Poles

Two-pole

Style type

Straight body

Cord range

0.22-0.66" in diameter

Material

Nylon

Packaging type

Core pack

Color

Black

Connection type

Screw

Allowable wire size

#16-12 AWG

NEMA configuration

Resources

Multimedia

Arrow Hart - Connecting Safety to Reliability since 1890

Specifications and datasheets

Industrial Grade Straight Blade Devices Spec Sheet

Eaton Specification Sheet - AH5666BK

6-15P

Torque rating

12-14 lbf-inch

Design type

Straight blade

Face/body material

Nylon

Receptacle type

Two-pole, three-wire, grounding



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)