

Eaton AH8200BK

Catalog Number: AH8200BK

Eaton Arrow Hart extra heavy-duty hospital grade standard duplex receptacle, #14-10 AWG, 15A, Healthcare, Flush, 125V, Back and side, Black, Brass, High-impact nylon face, Glass-filled nylon base, 5-15R, Duplex, Screw, Glass-filled nylon, Core pack



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Arrow Hart extra heavy-duty hospital grade standard duplex receptacle	AH8200BK
	UPC
	032664704505
Product Length/Depth	Product Height
1.32 in	4.19 in
Product Width	Product Weight
0.88 in	0.129 lb
Compliances	Certifications
RoHS Compliant	UL
	NOM
	Federal Specification Classification 6233 01

defaultTaxonomyAttributeLabel

Device type

Receptacle

Type

Duplex receptacle

Amperage Rating

15A

Voltage rating

125V

Contact material

Brass

Features

Auto-grounding

Terminal guards

Application

Healthcare

Device grade

Extra heavy-duty hospital grade

Wiring method

Back and side

Number of wires

3

Mounting method

Flush

Number Of Poles

Two-pole

Style type

Standard

Material

Glass-filled nylon

Packaging type

Core pack

Color

Black

Connection type

Screw

Resources

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Extra heavy-duty hospital grade straight blade receptacles spec](#)

[Eaton Specification Sheet - AH8200BK](#)

Allowable wire size

#14-10 AWG

NEMA configuration

5-15R

Design type

Straight blade

Face/body material

Glass-filled nylon base

High-impact nylon face

Receptacle type

Duplex



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)