

# Eaton AHIGL530P

Catalog Number: AHIGL530P

Eaton locking plug, 30A, Industrial, 125V, Orange, Single, L5-30, Two-pole, Three-wire, Glass-filled nylon

## General specifications



### Product Name

Eaton Arrow Hart ultra grip locking  
isolated ground plug

### Catalog Number

AHIGL530P

### UPC

032664739392

### Product Length/Depth

2.28 in

### Product Height

4.31 in

### Product Width

2.34 in

### Product Weight

0.33 lb

### Compliances

RoHS Compliant

### Certifications

UL

NOM

Federal Specification Classification 6233  
01

## defaultTaxonomyAttributeLabel

### Special features

Isolated ground

### Type

Locking plug

### Amperage Rating

30A

### Voltage rating

125 V

### Contact material

Brass

### Application

Industrial

### Device grade

Extra heavy-duty industrial specification grade

### Wiring method

Back

### Number of wires

Grounding

3

### Number Of Poles

Two-pole

### Color

Orange

### Cord diameter

0.38-1 in (9.5 mm-25.4 mm)

### Material

Glass filled nylon

### Operating temperature

-40 to 60 °C (-40 to 140 °F)

### Allowable wire size

#14-8 AWG

### NEMA configuration

L5-30

### Design type

Ultra grip

## Resources

### Multimedia

Arrow Hart - Connecting Safety to Reliability since 1890

### Specifications and datasheets

Eaton Specification Sheet - AHIGL530P

Industrial grade L5-30 locking devices spec sheet

Face/body material

Nylon



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)