

# Eaton AN11PB

Catalog Number: AN11PB

NEMA A200 Thermal Overload Relay, One-pole, Panel mounted, NEMA , Thermal Type A, Class 20, 1NC Auxiliary Contact, Alarm Contact (Form C) , Full load range .25-26.2A

## General specifications



Photo is representative

### Product Name

Eaton Freedom NEMA overload relay

### Catalog Number

AN11PB

### UPC

786678444437

### Product Length/Depth

4.8 in

### Product Height

2 in

### Product Width

3.8 in

### Product Weight

0.5 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

CSA Certified

UL Listed

Modification

1NC Auxiliary Contact, Alarm Contact (Form C)

Design

NEMA

Full load current range

.25-26.2A

Mounting

Panel

Number Of Poles

Single-pole

Special features

Heaters required

Trip Type

Thermal Type A, Class 20

Type

A200

Catalogs

Eaton's Volume 5—Motor Control and Protection

Installation instructions

Instructions for A200, A210, A250 size 6, two- or three-pole non-reversing or reversing motor controllers

Specifications and datasheets

Eaton Specification Sheet - AN11PB



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia