

Eaton AP40368

Catalog Number: AP40368

Eaton Crouse-Hinds series Arktite AP plug, 400A, 1.875-2.500", Two-wire, three-pole, 50-400 Hz, Style 2, Copper-free aluminum, Plug, 600 Vac/250 Vdc, 0.84"

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite AP plug	AP40368
	UPC
	782274045580
Product Length/Depth	Product Height
20.5 in	8 in
Product Width	Product Weight
8 in	26.2 lb

Photo is representative

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

3R

Product specifications

Amperage Rating

400A

Voltage rating

600 Vac/250 Vdc

Frequency rating

50 to 400 Hz

Grounding type

Style 2

Configuration

Two-wire, three-pole

Cable diameter

1.875-2.500"

Wire well size

0.84"

Material

Copper-free aluminum

Resources

3D CAD drawing package

[Eaton Crouse-Hinds AP40368 3D drawing](#)

Catalogs

[Arkrite 400A Metallic Plugs, Receptacles and Connectors catalog page](#)

Installation instructions

[IF 352 - Model M72 Arkrite Plugs and Receptacles](#)

[IF 852 - Arkrite AP Series, Model 80 200A/400A](#)

Specifications and datasheets

[Eaton Specification Sheet - AP40368](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)