

Eaton AP404512

Catalog Number: AP404512

Eaton Crouse-Hinds series Arktite AP plug, 400A, 3.0-3.8", Four-wire, four-pole, 50-400 Hz, Style 1, Copper-free aluminum, Plug, 600 Vac/250 Vdc, 1.25"

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite AP plug	AP404512
	UPC
	782274040806
Product Length/Depth	Product Height
20.5 in	8 in
Product Width	Product Weight
8 in	36.81 lb

Photo is representative

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

3R

Product specifications

Amperage Rating

400A

Voltage rating

600 Vac/250 Vdc

Frequency rating

50 to 400 Hz

Grounding type

Style 1

Configuration

Four-wire, four-pole

Cable diameter

3.0-3.8"

Wire well size

1.25"

Material

Copper-free aluminum

Resources

3D CAD drawing package

[Eaton Crouse-Hinds AP404512 3D drawing](#)

Catalogs

[Arkrite 400A Metallic Plugs, Receptacles and Connectors catalog page](#)

Installation instructions

[IF 352 - Model M72 Arkrite Plugs and Receptacles](#)

[IF 852 - Arkrite AP Series, Model 80 200A/400A](#)

Specifications and datasheets

[Eaton Specification Sheet - AP404512](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)