

# Eaton AP404610

Catalog Number: AP404610

Eaton Crouse-Hinds series Arktite AP plug, 400A, 2.5-3.0", Three-wire, four-pole, 50-400 Hz, Style 2, Copper-free aluminum, Plug, 600 Vac/250 Vdc, 1.25"

## General specifications



| Product Name                              | Catalog Number |
|---|----------------|
| Eaton Crouse-Hinds series Arktite AP plug | AP404610       |
|   | UPC            |
|   | 782274045603   |
| Product Length/Depth                      | Product Height |
| 20.5 in                                   | 8 in           |
| Product Width                             | Product Weight |
| 8 in                                      | 34 lb          |

Photo is representative

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### NEMA Rating

3R

## Product specifications

### Amperage Rating

400A

### Voltage rating

600 Vac/250 Vdc

### Frequency rating

50 to 400 Hz

### Grounding type

Style 2

### Configuration

Three-wire, four-pole

### Cable diameter

2.5-3.0"

### Wire well size

1.25"

### Material

Copper-free aluminum

## Resources

### 3D CAD drawing package

[Eaton Crouse-Hinds AP404610 3D drawing](#)

### Catalogs

[Arktite 400A Metallic Plugs, Receptacles and Connectors catalog page](#)

### Installation instructions

[IF 852 - Arktite AP Series, Model 80 200A/400A](#)

[IF 352 - Model M72 Arktite Plugs and Receptacles](#)

### Specifications and datasheets

[Eaton Specification Sheet - AP404610](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)