

Eaton APJ15487 S22

Catalog Number: APJ15487 S22

Eaton Crouse-Hinds series Arktite APJ plug, 150A, 0.875-1.70", Three-wire, four-pole, 50-400 Hz, Style 2, Copper-free aluminum, Reversed contacts, Plug, 600 Vac/250 Vdc

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite APJ plug	APJ15487 S22
	UPC
	662276213210
Product Length/Depth	Product Height
10.13 in	4.13 in
Product Width	Product Weight
4.13 in	4.96 lb

Photo is representative

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

4

Product specifications

Amperage Rating

150A

Voltage rating

600 Vac/250 Vdc

Frequency rating

50 to 400 Hz

Grounding type

Style 2

Configuration

Three-wire, four-pole

Cable diameter

0.875-1.70"

Material

Copper-free aluminum

Special features

Reversed contacts

Resources

Catalogs

[Arktite 150A Metallic Plugs, Receptacles and Connectors catalog page](#)

Certification reports

[Arktite Metallic Plugs, Receptacles and Connectors UL certification \(APJ\)](#)

Installation instructions

[IF 1564 - Arktite Plugs Model M4, 150A](#)

[IF 352 - Model M72 Arktite Plugs and Receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - APJ15487 S22](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)