

# Eaton APJ2251

Catalog Number: APJ2251

Eaton Crouse-Hinds series Arktite APJ plug, 20A, 0.25-0.50", Two-wire, two-pole, 50-400 Hz, Style 1, Copper-free aluminum, Without fastening ring, 600 Vac/250 Vdc

## General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite APJ plug	APJ2251
	UPC
	782274045207
Product Length/Depth	Product Height
5.56 in	2.81 in
Product Width	Product Weight
2.81 in	0.62 lb

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### NEMA Rating

4

## Product specifications

### Amperage Rating

20A

### Voltage rating

600 Vac/250 Vdc

### Frequency rating

50 to 400 Hz

### Grounding type

Style 1

### Configuration

Two-wire, two-pole

### Cable diameter

0.25-0.50"

### Material

Copper-free aluminum

### Special features

Without fastening ring

## Resources

### 3D CAD drawing package

[Eaton Crouse-Hinds APJ2251 3D drawing](#)

### Catalogs

[Arktite 20A Metallic Plugs, Receptacles and Connectors catalog page](#)

### Certification reports

[Arktite Metallic Plugs, Receptacles and Connectors UL certification \(APJ\)](#)

### Installation instructions

[IF 352 - Model M72 Arktite Plugs and Receptacles](#)

[IF 1338 - Arktite 20A Plugs, Receptacles and Cord Connectors](#)

### Specifications and datasheets

[Eaton Specification Sheet - APJ2251](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)