

Eaton APJ2273

Catalog Number: APJ2273

Eaton Crouse-Hinds series Arktite APJ plug, 20A, 0.50-0.87", Two-wire, two-pole, 50-400 Hz, Style 1, Copper-free aluminum, Fastening ring, 600 Vac/250 Vdc

General specifications



| Product Name | Catalog Number |
|--|----------------|
| Eaton Crouse-Hinds series Arktite APJ plug | APJ2273 |
| | UPC |
| | 782274045504 |
| Product Length/Depth | Product Height |
| 5.56 in | 2.81 in |
| Product Width | Product Weight |
| 2.81 in | 0.95 lb |

Photo is representative

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

4

Product specifications

Amperage Rating

20A

Voltage rating

600 Vac/250 Vdc

Frequency rating

50 to 400 Hz

Grounding type

Style 1

Configuration

Two-wire, two-pole

Cable diameter

0.50-0.87"

Material

Copper-free aluminum

Special features

Fastening ring

Resources

3D CAD drawing package

[Eaton Crouse-Hinds APJ2273 3D drawing](#)

Catalogs

[Arktite 20A Metallic Plugs, Receptacles and Connectors catalog page](#)

Certification reports

[Arktite Metallic Plugs, Receptacles and Connectors UL certification \(APJ\)](#)

Installation instructions

[IF 352 - Model M72 Arktite Plugs and Receptacles](#)

[IF 1338 - Arktite 20A Plugs, Receptacles and Cord Connectors](#)

Specifications and datasheets

[Eaton Specification Sheet - APJ2273](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)