

# Eaton APJ6585 S22

Catalog Number: APJ6585 S22

Eaton Crouse-Hinds series Arktite APJ plug, 60A, 0.75-1.45", Four-wire, five-pole, 50-400 Hz, Style 2, Copper-free aluminum, Reversed contacts, 600 Vac/250 Vdc

## General specifications



| Product Name                               | Catalog Number |
|--|----------------|
| Eaton Crouse-Hinds series Arktite APJ plug | APJ6585 S22    |
|  | UPC            |
|  | 782274584973   |
| Product Length/Depth                       | Product Height |
| 9 in                                       | 4.44 in        |
| Product Width                              | Product Weight |
| 4.44 in                                    | 3.62 lb        |

Photo is representative

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### NEMA Rating

4

## Product specifications

### Amperage Rating

60A

### Voltage rating

600 Vac/250 Vdc

### Frequency rating

50 to 400 Hz

### Grounding type

Style 2

### Configuration

Four-wire, five-pole

### Cable diameter

0.75-1.45"

### Material

Copper-free aluminum

### Special features

Reversed contacts

## Resources

### Catalogs

[Arktite 60A Metallic Plugs, Receptacles and Connectors catalog page](#)

### Certification reports

[Arktite Metallic Plugs, Receptacles and Connectors UL certification \(APJ\)](#)

### Installation instructions

[IF 352 - Model M72 Arktite Plugs and Receptacles](#)

[IF 1229 - Arktite Plugs and Receptacles, Model M4, 30, 60, 100A](#)

### Specifications and datasheets

[Eaton Specification Sheet - APJ6585 S22](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)