

Eaton APQ1037

Catalog Number: APQ1037

Eaton Crouse-Hinds series Arktite APQ motor plug, 100A, 0.875-1.70", Three-wire, three-pole, 50-400 Hz, Style 1, Copper-free aluminum, 600 Vac/250 Vdc



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite APQ motor plug	APQ1037
	UPC
	782274053301
Product Length/Depth	Product Height
4.25 in	4.25 in
Product Width	Product Weight
6.125 in	3.52 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

4

Product specifications

Amperage Rating

100A

Grounding type

Style 1

Configuration

Three-wire, three-pole

Cable diameter

0.875-1.70"

Material

Copper-free aluminum

Voltage rating

600 Vac/250 Vdc

Frequency rating

50 to 400 Hz

Resources

Catalogs

[Arktite APQ Circuit Breaking Motor Plugs catalog page](#)

Certification reports

[Arktite APQ Circuit Breaking Motor Plugs UL certification](#)

Specifications and datasheets

[Eaton Specification Sheet - APQ1037](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)