

# Eaton APQ347

Catalog Number: APQ347

Eaton Crouse-Hinds series Arktite APQ motor plug, 30A, 0.39-1.20", Four-wire, four-pole, 50-400 Hz, Style 1, Copper-free aluminum, 600 Vac/250 Vdc



Photo is representative

## General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite APQ motor plug	APQ347
	UPC
	782274052809
Product Length/Depth	Product Height
3.38 in	3.38 in
Product Width	Product Weight
3.63 in	1.44 lb

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### NEMA Rating

4

## Product specifications

### Amperage Rating

30A

### Grounding type

Style 1

### Configuration

Four-wire, four-pole

### Cable diameter

0.39-1.20"

### Material

Copper-free aluminum

### Voltage rating

600 Vac/250 Vdc

### Frequency rating

50 to 400 Hz

## Resources

### Catalogs

[Arktite APQ Circuit Breaking Motor Plugs catalog page](#)

### Certification reports

[Arktite APQ Circuit Breaking Motor Plugs UL certification](#)

### Specifications and datasheets

[Eaton Specification Sheet - APQ347](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)