

Eaton APQ348

Catalog Number: APQ348

Eaton Crouse-Hinds series Arktite APQ motor plug, 30A, 0.39-1.20", Three-wire, four-pole, 50-400 Hz, Style 2, Copper-free aluminum, 600 Vac/250 Vdc



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite APQ motor plug	APQ348
	UPC
	782274052908
Product Length/Depth	Product Height
3.38 in	3.38 in
Product Width	Product Weight
3.63 in	1.38 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

4

Product specifications

Amperage Rating

30A

Grounding type

Style 2

Configuration

Three-wire, four-pole

Cable diameter

0.39-1.20"

Material

Copper-free aluminum

Voltage rating

600 Vac/250 Vdc

Frequency rating

50 to 400 Hz

Resources

Catalogs

[Arktite APQ Circuit Breaking Motor Plugs catalog page](#)

Certification reports

[Arktite APQ Circuit Breaking Motor Plugs UL certification](#)

Specifications and datasheets

[Eaton Specification Sheet - APQ348](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)