

# Eaton APQ638

Catalog Number: APQ638

Eaton Crouse-Hinds series Arktite APQ motor plug, 60A, 0.50-1.45", Two-wire, three-pole, 50-400 Hz, Style 2, Copper-free aluminum, 600 Vac/250 Vdc



Photo is representative

## General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite APQ motor plug	APQ638
	UPC
	782274053059
Product Length/Depth	Product Height
4.25 in	4.25 in
Product Width	Product Weight
4.875 in	2.43 lb

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### NEMA Rating

4

## Product specifications

### Amperage Rating

60A

### Grounding type

Style 2

### Configuration

Two-wire, three-pole

### Cable diameter

0.50-1.45"

### Material

Copper-free aluminum

### Voltage rating

600 Vac/250 Vdc

### Frequency rating

50 to 400 Hz

## Resources

### Catalogs

[Arktite APQ Circuit Breaking Motor Plugs catalog page](#)

### Certification reports

[Arktite APQ Circuit Breaking Motor Plugs UL certification](#)

### Specifications and datasheets

[Eaton Specification Sheet - APQ638](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)