

# Eaton APR204212

Catalog Number: APR204212

Eaton Crouse-Hinds series Arktite APR connector, 200A, 1.875-2.500", Three-wire, four-pole, 50-400 Hz, Style 2, Copper-free aluminum, Crimp/solder, 600 Vac/250 Vdc, 0.75"

## General specifications



Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite APR connector	APR204212
	UPC
	782274191126
Product Length/Depth	Product Height
15.88 in	6.75 in
Product Width	Product Weight
6.75 in	12.8 lb

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### NEMA Rating

3R

## Product specifications

### Amperage Rating

200A

### Voltage rating

600 Vac/250 Vdc

### Frequency rating

50 to 400 Hz

### Grounding type

Style 2

### Configuration

Three-wire, four-pole

### Cable diameter

1.875-2.500"

### Termination style

Crimp/solder

### Wire well size

0.75"

### Material

Copper-free aluminum

## Resources

### Catalogs

[Arktite 200A Metallic Plugs, Receptacles and Connectors catalog page](#)

### Certification reports

[Arktite Metallic Plugs, Receptacles and Connectors UL certification \(APR\)](#)

### Installation instructions

[IF 854 - Arktite APR Series, Model 80 200A/400A](#)

### Specifications and datasheets

[Eaton Specification Sheet - APR204212](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)