

Eaton APR2251

Catalog Number: APR2251

Eaton Crouse-Hinds series Arktite APR connector, 20A, .250-.500", Two-wire, two-pole, 50-400 Hz, Copper-free aluminum, 600 Vac/250 Vdc

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite APR connector	APR2251
	UPC
	782274053707
Product Length/Depth	Product Height
5.56 in	2.81 in
Product Width	Product Weight
2.81 in	0.88 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

4

Product specifications

Amperage Rating

20A

Voltage rating

600 Vac/250 Vdc

Frequency rating

50 to 400 Hz

Configuration

Two-wire, two-pole

Cable diameter

.250-.500"

Material

Copper-free aluminum

Resources

3D CAD drawing package

[Eaton Crouse-Hinds APR2251 3D drawing](#)

Catalogs

[Arktite 20A Metallic Plugs, Receptacles and Connectors catalog page](#)

Certification reports

[Arktite Metallic Plugs, Receptacles and Connectors UL certification \(APR\)](#)

Installation instructions

[IF 1338 - Arktite 20A Plugs, Receptacles and Cord Connectors](#)

Specifications and datasheets

[Eaton Specification Sheet - APR2251](#)