

# Eaton APR2253

Catalog Number: APR2253

Eaton Crouse-Hinds series Arktite APR connector, 20A, .500-.850", Two-wire, two-pole, 50-400 Hz, Copper-free aluminum, 600 Vac/250 Vdc

## General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite APR connector	APR2253
	UPC
	782274053806
Product Length/Depth	Product Height
5.56 in	2.81 in
Product Width	Product Weight
2.81 in	0.52 lb

Photo is representative

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### NEMA Rating

4

## Product specifications

### Amperage Rating

20A

### Voltage rating

600 Vac/250 Vdc

### Frequency rating

50 to 400 Hz

### Configuration

Two-wire, two-pole

### Cable diameter

.500-.850"

### Material

Copper-free aluminum

## Resources

### 3D CAD drawing package

[Eaton Crouse-Hinds APR2253 3D drawing](#)

### Catalogs

[Arktite 20A Metallic Plugs, Receptacles and Connectors catalog page](#)

### Certification reports

[Arktite Metallic Plugs, Receptacles and Connectors UL certification \(APR\)](#)

### Installation instructions

[IF 1338 - Arktite 20A Plugs, Receptacles and Cord Connectors](#)

### Specifications and datasheets

[Eaton Specification Sheet - APR2253](#)