

Eaton APR3465 S22

Catalog Number: APR3465 S22

Eaton Crouse-Hinds series Arktite APR connector, 30A, 0.39-1.20", Three-wire, four-pole, 50-400 Hz, Style 2, Copper-free aluminum, Reversed contacts, 600 Vac/250 Vdc

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite APR connector	APR3465 S22
	UPC 782274458458
Product Length/Depth	Product Height
8.25 in	2.56 in
Product Width	Product Weight
2.56 in	1.92 lb

Photo is representative

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

4

Product specifications

Amperage Rating

30A

Voltage rating

600 Vac/250 Vdc

Frequency rating

50 to 400 Hz

Grounding type

Style 2

Configuration

Three-wire, four-pole

Cable diameter

0.39-1.20"

Material

Copper-free aluminum

Special features

Reversed contacts

Resources

Catalogs

[Arktite 30A Metallic Plugs, Receptacles and Connectors catalog page](#)

Certification reports

[Arktite Metallic Plugs, Receptacles and Connectors UL certification \(APR\)](#)

Installation instructions

[IF 1295 - Arktite APR 30, 60 and 100A Wiring Information](#)

Specifications and datasheets

[Eaton Specification Sheet - APR3465 S22](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)