Product specifications

Eaton APR3563

Catalog Number: APR3563

Eaton Crouse-Hinds series Arktite APR connector, 30A, 0.50-0.87", Four-wire, five-pole, 50-400 Hz, Style 2, Copper-free aluminum, 600 Vac/250 Vdc

Photo is representative

General specifications

Product Name	**Catalog Number**
Eaton Crouse-Hinds series Arktite APR connector	APR3563
	UPC
	782274055008
Product Length/Depth	**Product Height**
8.25 in	2.56 in
Product Width	**Product Weight**
2.56 in	1.86 lb

Powering Business Worldwide

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

4

Product specifications

Amperage Rating

30A

Voltage rating

600 Vac/250 Vdc

Frequency rating

50 to 400 Hz

Grounding type

Style 2

Configuration

Four-wire, five-pole

Cable diameter

0.50-0.87"

Material

Copper-free aluminum

Resources

3D CAD drawing package

Eaton Crouse-Hinds APR3563 3D drawing

Catalogs

Arktite 30A Metallic Plugs, Receptacles and Connectors catalog page

Certification reports

Arktite Metallic Plugs, Receptacles and Connectors UL certification (APR)

Installation instructions

IF 1295 - Arktite APR 30, 60 and 100A Wiring Information

Specifications and datasheets

Eaton Specification Sheet - APR3563

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Eaton.com/socialmedia