

# Eaton APR3565

Catalog Number: APR3565

Eaton Crouse-Hinds series Arktite APR connector, 30A, 0.87-1.38", Four-wire, five-pole, 50-400 Hz, Style 2, Copper-free aluminum, 600 Vac/250 Vdc

## General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite APR connector	APR3565
	UPC
	782274045931
Product Length/Depth	Product Height
8.25 in	2.56 in
Product Width	Product Weight
2.56 in	2.35 lb

Photo is representative

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### NEMA Rating

4

## Product specifications

### Amperage Rating

30A

### Voltage rating

600 Vac/250 Vdc

### Frequency rating

50 to 400 Hz

### Grounding type

Style 2

### Configuration

Four-wire, five-pole

### Cable diameter

0.87-1.38"

### Material

Copper-free aluminum

## Resources

### 3D CAD drawing package

[Eaton Crouse-Hinds APR3565 3D drawing](#)

### Catalogs

[Arktite 30A Metallic Plugs, Receptacles and Connectors catalog page](#)

### Certification reports

[Arktite Metallic Plugs, Receptacles and Connectors UL certification \(APR\)](#)

### Installation instructions

[IF 1295 - Arktite APR 30, 60 and 100A Wiring Information](#)

### Specifications and datasheets

[Eaton Specification Sheet - APR3565](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)