

Eaton APR404210

Catalog Number: APR404210

Eaton Crouse-Hinds series Arktite APR connector, 400A, 2.5-3.0", Three-wire, four-pole, 50-400 Hz, Style 2, Copper-free aluminum, 600 Vac/250 Vdc, 1.25"

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite APR connector	APR404210
	UPC 782274250069
Product Length/Depth	Product Height
20.25 in	7.75 in
Product Width	Product Weight
7.75 in	34 lb

Photo is representative

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Amperage Rating

400A

Voltage rating

600 Vac/250 Vdc

Frequency rating

50 to 400 Hz

Grounding type

Style 2

Configuration

Three-wire, four-pole

Cable diameter

2.5-3.0"

Wire well size

1.25"

Material

Copper-free aluminum

Resources

3D CAD drawing package

[Eaton Crouse-Hinds APR404210 3D drawing](#)

Catalogs

[Arktite 400A Metallic Plugs, Receptacles and Connectors catalog page](#)

Certification reports

[Arktite Metallic Plugs, Receptacles and Connectors UL certification \(APR\)](#)

Installation instructions

[IF 854 - Arktite APR Series, Model 80 200A/400A](#)

Specifications and datasheets

[Eaton Specification Sheet - APR404210](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)