

# Eaton APR40427

Catalog Number: APR40427

Eaton Crouse-Hinds series Arktite APR connector, 400A, 1.375-1.875", Three-wire, four-pole, 50-400 Hz, Style 2, Copper-free aluminum, 600 Vac/250 Vdc, 0.84"

## General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite APR connector	APR40427
	UPC
	782274045948
Product Length/Depth	Product Height
20.25 in	7.75 in
Product Width	Product Weight
7.75 in	28.22 lb

Photo is representative

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

## Product specifications

### Amperage Rating

400A

### Voltage rating

600 Vac/250 Vdc

### Frequency rating

50 to 400 Hz

### Grounding type

Style 2

### Configuration

Three-wire, four-pole

### Cable diameter

1.375-1.875"

### Wire well size

0.84"

### Material

Copper-free aluminum

## Resources

### 3D CAD drawing package

[Eaton Crouse-Hinds APR40427 3D drawing](#)

### Catalogs

[Arktite 400A Metallic Plugs, Receptacles and Connectors catalog page](#)

### Certification reports

[Arktite Metallic Plugs, Receptacles and Connectors UL certification \(APR\)](#)

### Installation instructions

[IF 854 - Arktite APR Series, Model 80 200A/400A](#)

### Specifications and datasheets

[Eaton Specification Sheet - APR40427](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)