

# Eaton APR6365

Catalog Number: APR6365

Eaton Crouse-Hinds series Arktite APR connector, 60A, 0.50-1.45", Two-wire, three-pole, 50-400 Hz, Style 2, Copper-free aluminum, 600 Vac/250 Vdc

## General specifications



| Product Name                                    | Catalog Number |
|---|----------------|
| Eaton Crouse-Hinds series Arktite APR connector | APR6365        |
|   | UPC            |
|   | 782274055602   |
| Product Length/Depth                            | Product Height |
| 6.5 in  | 2.94 in        |
| Product Width                                   | Product Weight |
| 2.94 in   | 3.45 lb        |

Photo is representative

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### NEMA Rating

4

## Product specifications

### Amperage Rating

60A

### Voltage rating

600 Vac/250 Vdc

### Frequency rating

50 to 400 Hz

### Grounding type

Style 2

### Configuration

Two-wire, three-pole

### Cable diameter

0.50-1.45"

### Material

Copper-free aluminum

## Resources

### 3D CAD drawing package

[Eaton Crouse-Hinds APR6365 3D drawing](#)

### Catalogs

[Arktite 60A Metallic Plugs, Receptacles and Connectors catalog page](#)

### Certification reports

[Arktite Metallic Plugs, Receptacles and Connectors UL certification \(APR\)](#)

### Installation instructions

[IF 1295 - Arktite APR 30, 60 and 100A Wiring Information](#)

### Specifications and datasheets

[Eaton Specification Sheet - APR6365](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)