

Eaton APR6455

Catalog Number: APR6455

Eaton Crouse-Hinds series Arktite APR connector, 60A, 0.50-1.45", Four-wire, four-pole, 50-400 Hz, Style 1, Copper-free aluminum, 600 Vac/250 Vdc

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite APR connector	APR6455
	UPC
	782274055800
Product Length/Depth	Product Height
8.25 in	2.94 in
Product Width	Product Weight
2.94 in	3.85 lb

Photo is representative

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

4

Product specifications

Amperage Rating

60A

Voltage rating

600 Vac/250 Vdc

Frequency rating

50 to 400 Hz

Grounding type

Style 1

Configuration

Four-wire, four-pole

Cable diameter

0.50-1.45"

Material

Copper-free aluminum

Resources

3D CAD drawing package

[Eaton Crouse-Hinds APR6455 3D drawing](#)

Catalogs

[Arktite 60A Metallic Plugs, Receptacles and Connectors catalog page](#)

Certification reports

[Arktite Metallic Plugs, Receptacles and Connectors UL certification \(APR\)](#)

Installation instructions

[IF 1295 - Arktite APR 30, 60 and 100A Wiring Information](#)

Specifications and datasheets

[Eaton Specification Sheet - APR6455](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)