

Eaton APRL20425

Catalog Number: APRL20425

Eaton Crouse-Hinds series Arktite APRL connector, 200A, 0.875-1.375", Three-wire, four-pole, 50-400 Hz, Style 2, Copper-free aluminum, Mechanical lug, 600 Vac/250 Vdc, 0.687"

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite APRL connector	APRL20425
	UPC
	662276214347
Product Length/Depth	Product Height
15.88 in	6.75 in
Product Width	Product Weight
6.75 in	14.96 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

3R

Product specifications

Amperage Rating

200A

Voltage rating

600 Vac/250 Vdc

Frequency rating

50 to 400 Hz

Grounding type

Style 2

Configuration

Three-wire, four-pole

Cable diameter

0.875-1.375"

Termination style

Mechanical lug

Wire well size

0.687"

Material

Copper-free aluminum

Resources

3D CAD drawing package

[Eaton Crouse-Hinds APRL20425 3D drawing](#)

Catalogs

[Arktite 200A Metallic Plugs, Receptacles and Connectors catalog page](#)

Certification reports

[Arktite Metallic Plugs, Receptacles and Connectors UL certification \(APR\)](#)

Installation instructions

[IF 854 - Arktite APR Series, Model 80 200A/400A](#)

[IF 352 - Model M72 Arktite Plugs and Receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - APRL20425](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)